


Emitator
SOEG-S-M18W-S-L
Numar piesa: 537695

FESTO



Fisa de date

Caracteristica	Valoare
Design	in jurul
Conform cu standardul	EN 60947-5-2
Autorizare	RCM Mark c UL us - Listed (OL)
Marca CE (consultati Declaratia de conformitate)	conform Directivei UE privind CEM
Variabila masurata	Pozitia
Principiul de masurare	optoelectronica
Metoda de masurare	Senzor cu fascicul transversal Emitator
Tipul de lumina	rosu
Autonomie	20000 mm
Temperatura ambianta	-25 °C...55 °C
Cadere de tensiune	2 V
Rezistenta la scurtcircuit	sincronizare
Domeniu de tensiune de lucru CC	10 V...36 V
Ondulatie remanenta	20 %
Curent fara sarcina	15 mA
Protectie la polaritate inversa	pentru toate conexiunile electrice
Conector electric	3 pini M12x1 Stecher
Dimensiune	M18x1
Tipul de montare	cu piulita de blocare
Cuplu de strangere	20 Nm
Greutate produs	57 g
Material carcasa	Alama cromat
Material piulita olandeza	Alama cromat
Temperatura ambientala cu traseu mobil al cablurilor	-5 °C...55 °C
Tip de protectie	IP65 IP67
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune

Caracteristica	Valoare
Conformitatea LABS	VDMA24364-B2-L