

Flansa oscilanta SNCL-20

Numar piesa: 537792

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	20
Pe baza standardului	ISO 21287
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...90 °C
Greutate produs	38 g
Nota privind materialele	Conform RoHS
Material fixare	Aliaj de aluminiu forjat
Material rulment	Material plastic
Material suruburi	Otel galvanizat