

Flansa oscilanta SNCL-12-R3

Numar piesa: 537794

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	12
Pe baza standardului	ISO 21287
Variante	Protectie anticoroziune ridicata
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...90 °C
Greutate produs	20 g
Nota privind materialele	Conform RoHS
Material fixare	Aliaj de aluminiu forjat cu capac de protectie
Material rulment	Material plastic
Material suruburi	otel inoxidabil inalt aliat