

## Flansa oscilanta SNCL-20-R3

Numar piesa: 537796

FESTO



### Fisa de date

| Caracteristica                       | Valoare                                           |
|--------------------------------------|---------------------------------------------------|
| Dimensiune                           | 20                                                |
| Pe baza standardului                 | ISO 21287                                         |
| Variante                             | Protectie anticoroziune ridicata                  |
| Clasa de rezistenta la coroziune KBK | 3 - stres intens de coroziune                     |
| Conformitatea LABS                   | VDMA24364-B2-L                                    |
| Temperatura ambianta                 | -40 °C...90 °C                                    |
| Greutate produs                      | 38 g                                              |
| Nota privind materialele             | Conform RoHS                                      |
| Material fixare                      | Aliaj de aluminiu forjat<br>cu capac de protectie |
| Material rulment                     | Material plastic                                  |
| Material suruburi                    | otel inoxidabil inalt aliat                       |