

Extindere amortizor zgomot UOMS-3/8

Numar piesa: 538437

FESTO



Fisa de date

Caracteristica	Valoare
Tip de garnitura la pivotul de insurubare	fara garnitura
Pozitie de instalare	orice
Structura constructiva	Amortizor de zgomot deschis
Presiune de functionare generator de vacuum	0 bar...8 bar
Presiune de operare a generatorului de vacuum	0 MPa...0.8 MPa 0 psi...116 psi
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	0 °C...60 °C
Tipul de montare	cu blocare
Greutate produs	17.5 g
Material insertie amortizor de zgomot	Spuma PU
Material pivot de insurubare	POM
Material carcasa	POM
Material teava interioara	Aliaj de aluminiu forjat