

# Priza MSSD-EB-M12

Numar piesa: 539712

FESTO



## Fisa de date

Caracteristica	Valoare
Frecventa de conectare	50
Tipul de montare	pe ventil electromagnetic cu surub central M2,5
Pozitie de instalare	orice
Greutate produs	11 g
Conector electric	3 pini Priza inclinata Formular C conform DIN EN 175301-803 design patrat
Presetupa	M12
Diametrul admisibil al cablului	4 mm...6 mm
Sectiune transversala a conectorului	1.5 mm <sup>2</sup>
Tip de protectie	IP65 conform IEC 60529
Temperatura ambianta	-40 °C...125 °C
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	Ranforsat cu PA
Material garnituri	HNBR