

Priza
MSSD-V-M16
Numar piesa: 539713

FESTO



Fisa de date

Caracteristica	Valoare
Frecventa de conectare	50
Tipul de montare	pe ventil electromagnetic cu surub central M3
Pozitie de instalare	orice
Greutate produs	35 g
Conector electric	3 pini Priza inclinata Forma B conform DIN EN 175301-803 design patrat
Presetupa	M16
Diametrul admisibil al cablului	6 mm...8 mm
Sectiune transversala a conectorului	0.75 mm ²
Tip de protectie	IP65 conform IEC 60529
Temperatura ambianta	-20 °C...115 °C
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	Ranforsat cu PA
Material garnituri	HNBR