


Numar piesa: 540041

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Mini
Seria	DB
Blocaj de actionare	Buton rotativ cu blocare
Pozitie de instalare	orice
Structura constructiva	pe bara P ventil de control cu piston cu actionare directa
Functia de regulator	Presiune de iesire constanta cu ventilare secundara cu comportament de curent invers
Presiune de lucru	0.15 MPa...1 MPa 1.5 bar...10 bar
Domeniu de reglare a presiunii	0.05 MPa...0.7 MPa 0.5 bar...7 bar 7.25 psi...101.5 psi
Histerezis max. de presiune	0.5 bar
Debit nominal standard (normalizat conform DIN 1343)	1000 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [-:~::~-]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-5 °C...50 °C
Temperatura ambianta	-5 °C...50 °C
Greutate produs	750 g
Tipul de montare	Instalarea panoului frontal cu accesorii
Conector pneumatic 1	G1/2
Conexiune pneumatica 2	G1/4
Material surub de inchidere	Otel galvanizat
Material bolt distantier	Aliaj de aluminiu forjat
Material bara de racordare	Aliaj de aluminiu forjat
Material inel de etansare	PVC
Material garnituri	NBR
Material carcasa	Ranforsat cu PA