

**Set manometru
DPA-40-16-MA-SET**

Numar piesa: 540782

FESTO



Fisa de date

Caracteristica	Valoare
Conform cu standardul	EN 837-1
Dimensiune nominala, manometru	27
Structura constructiva	Manometru cu tub Bourdon
Tipul de montare	cu filet exterior
Presiune de lucru	16 bar
Clasa de precizie de masurare	4
Tip de protectie	IP43
Temperatura ambianta	5 °C...60 °C
Conformitatea LABS	VDMA24364-B1/B2-L
Nota privind materialele	Conform RoHS
Pozitie de instalare	orice
Conexiune pneumatica	R1/8
Greutate produs	16 g