

Piesa cuplare KVI-CP-3-SSD

Numar piesa: 543252

FESTO



Fisa de date

Caracteristica	Valoare
Tipul de montare	cu filet exterior
Greutate produs	48 g
Conector electric	5 pini Priza Priza dreapta / Stecher drept M9 Stecher
Domeniu de tensiune de lucru CC	60 V
Tip de protectie	IP65 IP67
Temperatura ambianta	-20 °C...80 °C
Conformitatea LABS	VDMA24364-B2-L
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Material carcasa	Alama nichelat
Material garnituri	NBR
Pozitie de instalare	orice