

Cuplaj
EAMC-16-20-6-6
Numar piesa: 543420

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	6 mm
Diametru de montare 2	6 mm
Dimensiune	16
Lungime nominala	20 mm
Pozitie de instalare	orice
Turatie max.	10000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	0.28 kgmm ²
Cuplu transmisibil	1.6 Nm
Greutate produs	8 g
Nota privind materialele	Conform RoHS