

## Modul ramificare MS4-A-IPM-80

Numar piesa: 543498

**FESTO**



### Fisa de date

| Caracteristica                       | Valoare                                      |
|--------------------------------------|----------------------------------------------|
| Clasa de rezistenta la coroziune KBK | 2 - Solicitare moderata din cauza coroziunii |
| Conformitatea LABS                   | VDMA24364-B1/B2-L                            |
| Temperatura medie                    | -10 °C...60 °C                               |
| Greutate produs                      | 124 g                                        |
| Nota privind materialele             | Conform RoHS                                 |
| Materialul placii de racordare       | Aluminiu turnat sub presiune                 |
| Material garnituri                   | NBR                                          |
| Material surub tubular               | Aluminiu turnat sub presiune                 |
| Material conector module             | Aluminiu turnat sub presiune                 |
| Material suruburi                    | Otel                                         |