

Adaptor AD-G1-1NPT-I

Numar piesa: 546546

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	21.4 mm
Presiune de functionare interval complet de temperatura	-0.95 bar...10 bar
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Cuplu de strangere max. conexiune pneumatica 1	90 Nm
Cuplu de strangere max. conexiune pneumatica 2	35 Nm
Greutate produs	212.68 g
Conector pneumatic 1	Filet exterior G1
Conexiune pneumatica 2	Filet interior 1 NPT
Nota privind materialele	Conform RoHS
Material garnituri	PVC
Material carcasa	Otel galvanizat