

Adaptor NEFC-M12G5-0.3-U1G5

Numar piesa: 547432

FESTO



Fisa de date

Caracteristica	Valoare
Tipul de montare	insurubabil
Conector electric	5 pini M12x1 Stecher
Lungime cablu	0.3 m
Ansamblu cablu	4 x 0,34 mm ²
Tip de protectie	IP20
Temperatura ambianta	-5 °C...50 °C
Marca CE (consultati Declaratia de conformitate)	conform directivei RoHS a UE
Marca UKCA (consultati Declaratia de conformitate)	conform reglementarilor RoHS din UK
Conformitatea LABS	VDMA24364-B2-L
Nota privind materialele	Conform RoHS
Clasa de rezistenta la coroziune KBK	0 - nu este afectat de coroziune
Material manta de cablu	PUR
Material carcasa	ABS
Material contacte de cuplare	Alama, aurita