


Angrenaj|cutie de viteze|reductor|transmisie
EMGA-80-P-G3-SST-87

Numar piesa: 549432

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	80 mm
Dimensiune flansa motor	87 mm
Joc de rasucire	0.12 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	3:1
Turatie de lucru max.	7000 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	85 Nm
Momentul de inertie al reductorului	0.77 kgcm ²
Cuplu de iesire max.	136 Nm
Randament max.	98 %
Rigiditate la torsiune	6 Nm/arcmin
Greutate produs	2100 g
Interfata de iesire la unitatea de actionare	80G
Interfata reductor unitate de actionare	87A
Nota privind materialele	Conform RoHS