

## Bara de racordare VABM-C7-12M-G18-4

Numar piesa: 549641

**FESTO**



### Fisa de date

| Caracteristica                       | Valoare                                      |
|--------------------------------------|----------------------------------------------|
| Numarul max. de pozitii de ventil    | 4                                            |
| Clasa de rezistenta la coroziune KBK | 2 - Solicitare moderata din cauza coroziunii |
| Conformitatea LABS                   | VDMA24364-B2-L                               |
| Greutate produs                      | 122 g                                        |
| Conector pneumatic 1                 | G1/8                                         |
| Conexiune pneumatica 2               | M7                                           |
| Conector pneumatic 3                 | G1/8                                         |
| Nota privind materialele             | Conform RoHS                                 |
| Material bara de racordare           | Aliaj de aluminiu forjat                     |