

Bobina
MD-2-24VDC-PA

Numar piesa: 549903

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Ciclu de lucru	100%
Caracteristici bobina	24 V CC: 6,8 W
Fluctuatii de tensiune admise	+/- 10 %
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP65
Temperatura ambianta	-20 °C...50 °C
Cuplu de strangere max. conector cu filet	0.5 Nm
Greutate produs	110 g
Conector electric	conform DIN EN 175301-803
Tipul de montare	cu piulita randalinata
Nota privind materialele	Conform RoHS
Material bobina	Duroplast Cupru Otel
Material infasurare	Cupru