

Stecher FBS-RJ45-PP-GS

Numar piesa: 552000

FESTO



Fisa de date

Caracteristica	Valoare
Latime	30 mm
Inaltime	72 mm
Lungime	22 mm
Greutate produs	60 g
Nota privind interfata Fieldbus	PROFINET
Specificatie cablu Ethernet	Tip: CAT.5 Diametrul unui singur fir: max. 1,6 mm 0,13 - 0,36 mm ² , 7 fir 0,13 - 0,36 mm ² , 1 fir
Protectie contra atingerii directe si indirecte	PELV
Diametrul admisibil al cablului	5 mm...8 mm
Tip de protectie	IP65 IP67 conform IEC 60529
Temperatura ambianta	-40 °C...70 °C
Temperatura de depozitare	-40 °C...70 °C
Conformitatea LABS	VDMA24364-B2-L
Nota privind materialele	Conform RoHS
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Material carcasa	Zinc turnat sub presiune nichelat
Material garnituri	NBR
Material contacte de cuplare	Aliaj de cupru nichelat si aurit