


Angrenaj|cutie de viteze|reductor|transmisie EMGA-60-P-G5-SAS-55

Numar piesa: 552189

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	60 mm
Dimensiune flansa motor	55 mm
Joc de rasucire	0.17 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	5:1
Turatie de lucru max.	13000 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	22 Nm
Momentul de inertie al reductorului	0.078 kgcm ²
Cuplu de iesire max.	35.2 Nm
Randament max.	98 %
Rigiditate la torsiune	2.3 Nm/arcmin
Greutate produs	900 g
Interfata de iesire la unitatea de actionare	60G
Interfata reductor unitate de actionare	55A
Nota privind materialele	Conform RoHS