

Amortizor de zgomot UOS-1

Numar piesa: 552252

FESTO



Fisa de date

Caracteristica	Valoare
Tip de garnitura la pivotul de insurubare	fara garnitura
Pozitie de instalare	orice
Structura constructiva	Amortizor de zgomot deschis
Presiune de lucru	0 MPa...1 MPa 0 bar...10 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [-:::-]
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B1/B2-L
Nivel de presiune acustica	75 dB(A)
Temperatura ambianta	-10 °C...50 °C
Tipul de montare	cu filet exterior
Greutate produs	200 g
Conexiune pneumatica	G1
Material insertie amortizor de zgomot	PE
Nota privind materialele	Conform RoHS
Material carcasa	POM
Material manson	Aliaj de aluminiu forjat