

Fibra optica
S00C-DS-P-M4-2-R15
Numar piesa: 552805

FESTO



Fisa de date

Caracteristica	Valoare
Nota privind materialele	Conform RoHS
Metoda de masurare	Senzor de reflexie
Diametru minim al obiectului	0.1 mm
Fibra optica - caracteristica speciala	Precizie
Autonomie	65 mm
Temperatura ambianta	-55 °C...70 °C
Dimensiune cap	M4
Lungimea fibrei optice	2 m
Raza min. de indoire	15 mm
Cuplu de strangere max.	2 Nm
Ø exterior	1 mm
Material carcasa	otel inoxidabil inalt aliat
Material fibra optica	PE
Tip de protectie	IP66
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364 zona III