

Fibra optica SOOC-TB-P-C5-2-R10

Numar piesa: 552828

FESTO



Fisa de date

Caracteristica	Valoare
Nota privind materialele	Conform RoHS
Metoda de masurare	Bariera luminoasa tip furca
Diametru minim al obiectului	0.2 mm
Fibra optica - caracteristica speciala	Bariera luminoasa tip furca
Autonomie	5 mm
Temperatura ambianta	-55 °C...70 °C
Dimensiune cap	Dreptunghi 41x15x7 mm Groapa furcii 5x29 mm
Lungimea fibrei optice	2 m
Raza min. de indoire	10 mm
Ø exterior	1.25 mm
Material carcasa	ABS
Material fibra optica	PE
Tip de protectie	IP66
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364 zona III