

Fibra optica
S00C-DS-M6-2-R25
Numar piesa: 552836

FESTO



Fisa de date

Caracteristica	Valoare
Nota privind materialele	Conform RoHS
Metoda de masurare	Senzor de reflexie
Diametru minim al obiectului	0.1 mm
Fibra optica - caracteristica speciala	Standard
Autonomie	140 mm
Temperatura ambianta	-55 °C...70 °C
Dimensiune cap	M6x0,75
Lungimea fibrei optice	2 m
Raza min. de indoire	25 mm
Cuplu de strangere max.	3 Nm
Ø exterior	2.2 mm
Material carcasa	Aliaj de cupru PVC nichelat
Material fibra optica	PE
Tip de protectie	IP66
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364 zona III