

Tub plastic PAN

Numar piesa: 553610

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	4 mm...16 mm
Ø interior	2.5 mm...12 mm
Conform cu standardul	DIN 73378-PA12-PHL
Presiune de lucru in functie de temperatura	-0.95 bar...35 bar
Autorizare	TÜV
Organizatia emitenta a certificatului	B 013277 0506 00
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Ulei mineral
Conformitatea LABS	VDMA24364-B2-L
Clasa de puritate a incaperii	Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1
Temperatura ambianta	-60 °C...100 °C
Culoare	albastru maro galben verde natura rosu negru argintiu alb
Nota privind materialele	Conform RoHS
Material furtun	PA12-P TPE-A