

Tub plastic PEN

Numar piesa: 553769

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	4 mm...16 mm
Ø interior	2.7 mm...10.8 mm
Proprietati ale furtunului	lant energetic adecvat
Presiune de lucru in functie de temperatura	-0.95 bar...10 bar
Autorizare	TÜV
Organizatia emitenta a certificatului	B 013277 0506 00
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Apa (lichida, fara gheata)
Conformitatea LABS	VDMA24364-B2-L
Clasa de puritate a incaperii	Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1
Temperatura ambianta	-30 °C...60 °C
Culoare	albastru galben verde natura rosu negru argintiu alb
Duritate Shore	D 52 +/-3
Nota privind materialele	Conform RoHS
Material furtun	PE