

Tub plastic PLN

Numar piesa: 553850

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	4 mm...16 mm
Ø interior	2.9 mm...12 mm
Presiune de lucru in functie de temperatura	-0.95 bar...14 bar
Autorizare	TÜV
Organizatia emitenta a certificatului	B 013277 0506 00
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Apa (lichida, fara gheata)
Conformitatea LABS	VDMA24364-B2-L
Clasa de puritate a incaperii	Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	-30 °C...80 °C
Culoare	albastru maro galben verde natura rosu negru argintiu alb
Nota privind materialele	Conform RoHS
Material furtun	PE