

**Tub plastic**  
**PAN-10X1,5-SW-300**  
Numar piesa: 553903

**FESTO**



**Fisa de date**

| Caracteristica                              | Valoare                                                               |
|---------------------------------------------|-----------------------------------------------------------------------|
| Ø exterior                                  | 10 mm                                                                 |
| raza de indoire relevanta pentru debit      | 58 mm                                                                 |
| Ø interior                                  | 7 mm                                                                  |
| Raza min. de indoire                        | 27 mm                                                                 |
| Proprietati ale furtunului                  | lant energetic adecvat                                                |
| Presiune de lucru in functie de temperatura | -0.095 MPa...1.7 MPa<br>-0.95 bar...17 bar<br>-13.775 psi...246.5 psi |
| Autorizare                                  | TÜV                                                                   |
| Organizatia emitenta a certificatului       | B 013277 0506 00                                                      |
| Mediu de operare                            | Aer comprimat conform ISO 8573-1:2010 [7:-:-]                         |
| Conformitatea LABS                          | VDMA24364-B2-L                                                        |
| Temperatura ambianta                        | -30 °C...80 °C                                                        |
| Greutatea produsului in functie de lungime  | 0.042 kg/m                                                            |
| Conexiune pneumatica                        | pentru conector cu Ø exterior de 10 mm                                |
| Culoare                                     | negru                                                                 |
| Duritate Shore                              | D 55 +/-3                                                             |
| Nota privind materialele                    | Conform RoHS                                                          |
| Material furtun                             | TPE-A                                                                 |