

Suport lagar LSN-100

Numar piesa: 5566

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	100
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...120 °C
Sarcina admisibila maxima	9 kN
Greutate produs	1169 g
Nota privind materialele	Conform RoHS
Material fixare	Fonta ductila
Material bucsa	Aliaj de aluminiu forjat
Material rulment articulat	Otel PTFE