

Cuplaj
EAMD-19-15-9-8X10
Numar piesa: 557999

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	9 mm
Diametru de montare 2	8 mm
Dimensiune	19
Lungime nominala	15 mm
Pozitie de instalare	orice
Turatie max.	10000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	0.445 kgmm ²
Cuplu transmisibil	2 Nm
Greutate produs	13.5 g
Nota privind materialele	Conform RoHS