

Fus de arbore EAMB-18-9-8X16-10X12

Numar piesa: 558035

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	8 mm
Diametru de montare 2	10 mm
Dimensiune	70
Lungime nominala	16 mm
Pozitie de instalare	orice
Turatie max.	8000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	0.838 kgmm ²
Cuplu transmisibil	12 Nm
Greutate produs	29 g
Nota privind materialele	Conform RoHS