

Fus de arbore EAMB-24-6-15X21-16X20

Numar piesa: 558036

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	15 mm
Diametru de montare 2	16 mm
Dimensiune	80
Lungime nominala	21 mm
Pozitie de instalare	orice
Turatie max.	8000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	3.1 kgmm ²
Cuplu transmisibil	29 Nm
Greutate produs	68 g
Nota privind materialele	Conform RoHS