

Fus de arbore EAMB-34-6-25X26-23X27

Numar piesa: 558037

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	25 mm
Diametru de montare 2	23 mm
Dimensiune	120
Lungime nominala	26 mm
Pozitie de instalare	orice
Turatie max.	5500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	18.2 kgmm ²
Cuplu transmisibil	100 Nm
Greutate produs	201 g
Nota privind materialele	Conform RoHS