

Fus de arbore EAMB-44-7-35X30-32X32

Numar piesa: 558038

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	35 mm
Diametru de montare 2	32 mm
Dimensiune	185
Lungime nominala	30 mm
Pozitie de instalare	orice
Turatie max.	4500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	75.3 kgmm ²
Cuplu transmisibil	200 Nm
Greutate produs	463 g
Nota privind materialele	Conform RoHS