


Carcasa cuplaj EAMK-A-D32-35A-40A

Numar piesa: 560280

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-10 °C...60 °C
Greutate produs	115 g
Cod de interfata actuator	D32C
Cod de interfata carcasa de cuplare	40A
Nota privind materialele	Conform RoHS