


Set axial EAMM-A-K38-87A

Numar piesa: 560682

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Cuplu transmisibil	4.4 Nm
Greutate produs	380 g
Cod de interfata actuator	K38
Codul interfetei motor In	87A
Nota privind materialele	Conform RoHS