

Tirant
VMPAL-ZAS-645

Numar piesa: 561132

FESTO



Fisa de date

Caracteristica	Valoare
Lungime	645 mm
Unitate de ambalare	3
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-5 °C...50 °C
Cuplu de strangere max.	1.7 Nm
Greutate produs	432 g
Nota privind materialele	Conform RoHS
Material tirant	otel inoxidabil aliaj inalt