


Set axial EAMM-A-P4-28B-40A

Numar piesa: 562637

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	8.3 mm
Pozitie de instalare	orice
Turatie max.	10000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	0.28 kgmm ²
Cuplu transmisibil	0.7 Nm
Greutate produs	50 g
Cod de interfata actuator	P4-28B
Codul interfetei motor In	40A
Cod de interfata carcasa de cuplare	28B
Nota privind materialele	Conform RoHS