

Adaptor NPFV-AF-G14-N14-MF

Numar piesa: 563397

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	6 mm
Presiune de lucru	0.2 MPa...0.8 MPa 2 bar...8 bar
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364 zona III
Conector pneumatic 1	G1/4
Conexiune pneumatica 2	1/4 NPT
Nota privind materialele	Conform RoHS
Material adaptor	otel inoxidabil inalt aliat
Material garnituri	NBR