

Manometru PAGN-26-1.6M-P10

Numar piesa: 563735

FESTO



Fisa de date

Caracteristica	Valoare
Interval de afisare	0 MPa...1.6 MPa
Dimensiune nominala, manometru	26
Protectie la explozie	Respectati informatiile din certificat Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Structura constructiva	Manometru cu tub Bourdon
Tipul de montare	Instalarea liniei
Mediu de operare	Gaze inerte lichide neutre
Nota referitoare la mediul de lucru/comanda	fara acetilena fara oxigen
Presiune de lucru	0 MPa...1.6 MPa 0 bar...16 bar 0 psi...232 psi
Factor de incarcare alternanta	0.66
Clasa de precizie de masurare	5
Tip de protectie	IP43
Temperatura medie	-20 °C...60 °C
Temperatura ambianta	-20 °C...60 °C
Conformitatea LABS	VDMA24364-B1/B2-L
Nota privind materialele	Conform RoHS
Pozitie de conectare	Partea din spate, centrat
Conexiune pneumatica	Cartus 10 mm
Materiale care intra in contact cu mediul	Alama
Material pivot de insurubare	Alama
Material carcasa	PA
Material vizor	PS
Culoarea carcasei	negru
Greutate produs	15 g

Caracteristica	Valoare
Scala	Scara unica MPa (exterior)