


## Set axial EAMM-A-P10-38A-87A

Numar piesa: 564999

**FESTO**



### Fisa de date

| Caracteristica                      | Valoare                |
|-------------------------------------|------------------------|
| Lungime nominala                    | 18 mm                  |
| Pozitie de instalare                | orice                  |
| Turatie max.                        | 8000 1/min             |
| Conformitatea LABS                  | VDMA24364-B2-L         |
| Temperatura de depozitare           | -25 °C...60 °C         |
| Umiditate relativa                  | 0 - 95 %               |
| Tip de protectie                    | IP40                   |
| Temperatura ambianta                | -10 °C...60 °C         |
| Momentul de inertie al masei        | 5.87 kgmm <sup>2</sup> |
| Cuplu transmisibil                  | 12.5 Nm                |
| Greutate produs                     | 380 g                  |
| Cod de interfata actuator           | P10-38A                |
| Codul interfetei motor In           | 87A                    |
| Cod de interfata carcasa de cuplare | 38A                    |
| Nota privind materialele            | Conform RoHS           |