

Racord L CRQSL-3/8-1/2-U

Numar piesa: 565332

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Standard
Latimea nominala	0.413 țol
Pozitie de instalare	orice
Design	Forma L
Unitate de ambalare	1
Structura constructiva	Principiul push-pull
Presiune de functionare interval complet de temperatura	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364 zona III
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	-20 °C...150 °C
Cuplu de strangere max.	13.3 ft-lbf
Greutate produs	2.37 oz
Cabluri utilizabile	PFAN
Tipul de montare	Hexagon extern 13/16
Conector pneumatic 1	Filet exterior 3/8 NPTF
Conexiune pneumatica 2	pentru furtun cu Ø exterior 1/2"
Temperatura ambientala Fahrenheit	-4 °F...302 °F
Nota privind materialele	Conform RoHS
Material carcasa	otel inoxidabil inalt aliat
Material inel detasabil	otel inoxidabil aliaj inalt
Material garnitura furtun	FPM
Material segment de prindere a furtunului	otel inoxidabil aliaj inalt