

Tub plastic PEN-.-U

Numar piesa: 567448

FESTO



Fisa de date

Caracteristica	Valoare
Proprietati ale furtunului	lant energetic adecvat
Presiune de functionare interval complet de temperatura	-0.095 MPa...0.4 MPa -0.95 bar...4 bar -13.775 psi...58 psi
Presiune de lucru in functie de temperatura	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Indicatie referitoare la presiunea de lucru	Apa: max. 0,6 MPa la 0 - 50 °C
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Apa (lichida, fara gheata)
Conformitatea LABS	VDMA24364-B2-L
Clasa de puritate a incaperii	Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1
Temperatura ambianta	-22 °F...140 °F
Culoare	albastru maro galben verde natura rosu negru argintiu alb
Nota privind materialele	Conform RoHS
Material furtun	PE