

Tub plastic PLN-.-U

Numar piesa: 567449

FESTO



Fisa de date

Caracteristica	Valoare
Presiune de functionare interval complet de temperatura	-0.095 MPa...0.7 MPa -0.95 bar...7 bar -13.775 psi...101.5 psi
Presiune de lucru in functie de temperatura	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Indicatie referitoare la presiunea de lucru	Apa: max. 0,6 MPa la 0 - 50 °C
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:::] Apa (lichida, fara gheata)
Conformitatea LABS	VDMA24364-B2-L
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	-22 °F...178 °F
Culoare	albastru maro galben verde natura rosu negru argintiu alb
Nota privind materialele	Conform RoHS
Material furtun	PE