

Tub plastic PAN-MF-12X1,5-SW

Numar piesa: 570361

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	12 mm
raza de indoire relevanta pentru debit	70 mm
Ø interior	9 mm
Raza min. de indoire	50 mm
Conform cu standardul	DIN 73378-PA12-PHL
Proprietati ale furtunului	lant energetic adecvat
Presiune de lucru in functie de temperatura	-0.095 MPa...1.9 MPa -0.95 bar...19 bar -13.775 psi...275.5 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Ulei mineral
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-60 °C...100 °C
Greutatea produsului in functie de lungime	0.051 kg/m
Conexiune pneumatica	pentru racordul push-in cu Ø exterior de 12 mm
Culoare	negru
Duritate Shore	D 65 +/-3
Nota privind materialele	Conform RoHS
Material furtun	PA12-P