

Tub plastic
PAN-MF-4X0,75-SW-500
Numar piesa: 572091

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	4 mm
raza de indoire relevanta pentru debit	15 mm
Ø interior	2.5 mm
Raza min. de indoire	10 mm
Conform cu standardul	DIN 73378-PA12-PHL
Proprietati ale furtunului	lant energetic adecvat
Presiune de lucru in functie de temperatura	-0.095 MPa...3.1 MPa -0.95 bar...31 bar -13.775 psi...449.5 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Ulei mineral
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-60 °C...100 °C
Greutatea produsului in functie de lungime	0.008 kg/m
Conexiune pneumatica	pentru racordul push-in cu Ø exterior de 4 mm
Culoare	negru
Duritate Shore	D 65 +/-3
Nota privind materialele	Conform RoHS
Material furtun	PA12-P