

Tub plastic PAN-MF-6X1-SW-500

Numar piesa: 572093

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	6 mm
raza de indoire relevanta pentru debit	35 mm
Ø interior	4 mm
Raza min. de indoire	15 mm
Conform cu standardul	DIN 73378-PA12-PHL
Proprietati ale furtunului	lant energetic adecvat
Presiune de lucru in functie de temperatura	-0.095 MPa...2.7 MPa -0.95 bar...27 bar -13.775 psi...391.5 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Ulei mineral
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-60 °C...100 °C
Greutatea produsului in functie de lungime	0.016 kg/m
Conexiune pneumatica	pentru racord cu Ø exterior de 6 mm
Culoare	negru
Duritate Shore	D 65 +/-3
Nota privind materialele	Conform RoHS
Material furtun	PA12-P