

Interfata bus CDPX-F-CO

Numar piesa: 575301

FESTO



Fisa de date

Caracteristica	Valoare
Adancimea de instalare	24 mm
Inaltime	91 mm
Lungime	41 mm
Autorizare	C-Tick c UL us - Listed (OL)
Marca CE (consultati Declaratia de conformitate)	conform Directivei UE privind CEM conform directivei RoHS a UE
Marca UKCA (consultati Declaratia de conformitate)	conform reglementarilor UK privind EMC conform reglementarilor RoHS din UK
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-20 °C...70 °C
Umiditate relativa	5 - 85 % fara condensare
Tip de protectie	IP20
Temperatura ambianta	0 °C...50 °C
Greutate produs	150 g
Nota privind materialele	Conform RoHS
Interfata Fieldbus, tip	CANopen
Interfata Fieldbus, tehnologie de conectare	Stecher Sub-D 9 pini
Interfata Fieldbus, viteza de transmisie	9,6 kbit/s pana la 1 Mbit/s