



Fisa de date

Caracteristica	Valoare
Inaltime	39,4 mm
Lungime	58 mm
Greutate produs	24 g
Interfata Fieldbus	Sub-D, 9 pini, priza
Conector electric	9 pini / 9 pini Sub-D / terminal cu surub
Rata baud	1 Mbit/s
Diametrul admisibil al cablului	8 mm 8 mm
Tip de protectie	IP40
Temperatura ambianta	-20 °C...70 °C
Marca CE (consultati Declaratia de conformitate)	conform Directivei UE privind joasa tensiune
Conformitatea LABS	VDMA24364-B2-L
Nota privind materialele	Conform RoHS
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune