

Placa racordare VMPAC-AP-14-SP-1

Numar piesa: 576576

FESTO



Fisa de date

Caracteristica	Valoare
Latime	32.8 mm
Lungime	169 mm
Dimensiune grila	26.8 mm
Numarul max. de pozitii de ventil	1
Presiune de lucru	-0.9 bar...8 bar
Presiunea de control	3 bar...8 bar
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-5 °C...50 °C
Greutate produs	160 g
Conector pneumatic 1	G1/4
Conexiune pneumatica 2	G1/4
Conector pneumatic 3	G1/4
Conexiune pneumatica 4	G1/4
Conexiune pneumatica 5	G1/4
Nota privind materialele	Conform RoHS
Material carcasa	Ranforsat cu PA