

Amortizor de zgomot UC-3/8-20

Numar piesa: 576759

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Unitate de ambalare	20
Presiune de lucru	0 MPa...1 MPa 0 bar...10 bar
Debit in raport cu atmosfera	5000 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Nota referitoare la mediul de lucru/comanda	Este posibila functionarea cu ulei
Conformitatea LABS	VDMA24364-B1/B2-L
Nivel de presiune acustica	60 dB(A)
Temperatura ambianta	-10 °C...70 °C
Greutate produs	10.5 g
Conexiune pneumatica	G3/8
Material insertie amortizor de zgomot	PE
Material pivot de insurubare	PE
Nota privind materialele	Conform RoHS